

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0505447525](#)
Status: **Obsolete**
Description: Ring Tongue Terminal for 250-300MCM AWG, Closed Uninsulated Brazed Barrel, Stud Size M14, Oxygen-Free Copper, Length 66.00mm (2.598")

Documents:
[Drawing \(PDF\)](#)

General	
Product Family	Ring and Spade Terminals
Series	50544
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	M14
Wire Size AWG	250MCM, 300MCM
Wire Size mm²	117.2 - 152.05
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-50541-002
Sales Drawing	SD-50544-001



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[50544Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan	
Description	Product #
Tool Kit For 57343-9012	0573439001
Battery Type Hand Crimper For JIS Terminal	0573439004