





OBSOLETE	10.3±3 GRAMS	5.00±0.08 [.197±.003]	#10	BODY: COPPER ASTM-B187 ANNEALED	277147-5
	-	8.33±0.13 [.328±.005]	5/16	TIN PL MIL-T-10727 0.00381[.000150] MIN THK	277147-4
	-	6.73±0.13 [.265±.005]	1/4	INSERT & FUNNEL: BRASS ASTM B36	277147-3
	10.0±3 GRAMS	9.91±0.13 [.390±.005]	3/8	NICKEL PL SAE AMS QQ-N-290A,	277147-2
	11.0±3 GRAMS	5.00±0.08 [.197±.003]	#10	DATED JULY 2000,	277147-1
				0.00254 [.000100] MIN THK	
WEIGHT		'A'	'B'	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 6/23/89 DK SCHRUM		Tyco Electronics Corporation Harrisburg, PA 17105-3608					
DIMENSIONS: MM [INCHES]		CHK 10/16/90 MS FEHER		NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM, 8.6mm2 [8] ALUMINIUM 4.8mm2 [10] COPPER					
		APVD 10/23/90 AJ KAUFMAN							
		PRODUCT SPEC 108-11011							
		APPLICATION SPEC 114-2134							
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C-277147	RESTRICTED TO -		
				CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV N