


PTV - External Air Sensor (Fast Response)

External Air Sensor With Fast Response - For measurement of temperatures in refrigerated holds, cargo and freeze compartments, or as a general purpose air sensor, etc...,


- Resistance type PT100, Class B, 4 wire (Glass Detector)
- Sheath dimensions are 8 mm dia stainless steel x 50mm in length. This sensor has a perforated tip for fast response
- The connection box is a marine box of grey-enamelled light-alloy metal, protection IP67
- Temp Range : -40°C to +80°C
- Approvals: Lloyd's Register of Shipping




Global Part No.	Description
91-9414-03	External Air Sensor (Fast Response)



ALL DIMENSIONS METRIC



DO NOT SCALE



ISSUE	MODIFICATION	DRAWN	APP	DATE	SHEET 1 OF 1 SHEETS	THIS DRAWING REMAINS THE PROPERTY OF GLOBAL LIMITED AND MAY NOT BE REPRODUCED WITHOUT OUR PERMISSION.			GLOBAL MEASUREMENT AND CONTROL LTD. UNIT 17, FORD LANE BUSINESS PARK FORD LANE, BR ARUNDEL WEST SUSSEX BN18 0JZ TELEPHONE: 01243 555277 FAX: 01243 555177		
1	For Reference Only	S.A.	S.A.	10/01/05	MATERIAL	TOLERANCE	TITLE	DRAWN		CHECKED	DATE
2						X ± 0.50 X.X ± 0.25 X.XX ± 0.10	External Air Sensor	S.A.			10.01.05
3					FINISH CLEAN & BURR FREE	PART NUMBER	91-9414-03	DRAWING NUMBER			
4						SCALE	N.T.S.	CUST PART NO		XX-XXXX-XX	