

GP Batteries

Data Sheet

Model No.: GP15A

NO MERCURY ADDED

Description : Mercury & Cadmium Free Alkaline
Manganese Battery, AA Size

Chemical System : Alkaline Manganese

Nominal Voltage : 1.5 Volts

Nominal Dimensions: Ø14.5 mm x 50.5 mm

Terminals : Protruded positive(+) and flat negative(-)
contacts

Jacket : Foil jacket


Applications : All electronic devices, e.g. toys,
photographic equipment, data banks,
calculators, audio appliances, remote
controls, paging machines.

Warranty Period : 36 months

Average Weight : 23g

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
10 Ohms	24 Hrs/Day	0.9V	17.0Hrs



At 20±2°C within 30 days of manufacture

Cross References:

GP	JIS	IEC	Eveready	Duracell
15A	LR6	LR6	E91	MN1500

