

381 Remote Display True-rms AC/DC Clamp Meter with iFlex™

The first clamp meter with a detachable, remote display for easier, faster, safer measurements

The new Fluke 381 does everything you would expect from a clamp meter, and then lets you remove the display for even more flexibility. Now one technician can do jobs that used to require two people; clamp the Fluke 381 around a conductor, remove the display and walk across the room to operate controls or remove protective equipment, all while watching real-time readings. The new iFlex™ flexible current probe (included) expands the measurement range to 2500 A ac while providing increased display flexibility, ability to measure awkward sized conductors and improved wire access.

New



**True
RMS**



Technical Data

Measurement capability

- 1000 A ac and dc current measurement with fixed jaw
- 2500 A ac current measurement with iFlex™ flexible current probe
- 1000 V ac and dc voltage measurement
- True-rms ac voltage and current for accurate measurements on non-linear signals
- Frequency measurement to 500 Hz with both jaw and iFlex™
- 60 kΩ resistance measurement with continuity detection
- Min, max, average and inrush recording to capture variations automatically

Features

- Wireless technology allows the display to be carried up to 30 ft away from the point of measurement for added flexibility without interference with measurement accuracy
- iFlex™ flexible current probe expands the measurement range to 2500 A ac while providing increased display flexibility, ability to measure awkward sized conductors and improved wire access
- CAT IV 600V, CAT III 1000 V safety rating
- Integrated low pass filter and state of the art signal processing allows for use in noisy electrical environments while providing stable readings

- Proprietary inrush measurement technology to filter out noise and capture motor starting current exactly as the circuit protection sees it
- Ergonomic design fits in your hand and can be used while wearing personal protective equipment
- The removable magnetic display can be conveniently mounted where it is easily seen
- Radio transmitter automatically turns off when the display is connected to the meter
- Large, easy to read, backlight display automatically sets the correct measurement range so you do not need to change switch positions while taking a measurement
- Three-year warranty
- Soft carrying case

Ordering information

381 Remote Display True-rms Clamp Meter with iFlex™

Specifications

Fluke 381	Range	Resolution	Accuracy
AC current via jaw	999.9 A	0.1 A	2 % ± 5 digits
AC current via iFlex™	2500 A	0.1 A	3 % ± 5 digits
DC current	999.9 A	0.1 A	2 % ± 5 digits
AC voltage	1000 V	0.1 V	1.5 % ± 5 digits
DC voltage	1000 V	0.1 V	1 % ± 5 digits
Resistance	60,000 Ω	0.1 Ω	1 % ± 5 digits
Frequency	500 Hz	0.1 Hz	0.5 % ± 5 digits
True-rms	•		
Continuity	•		
Hold	•		
Backlight	•		
Min/Max	•		
Inrush	•		
Low pass filter	•		
Removable wireless display	•		
18 inch iFlex™ Flexible Current Probe	Included		
10 inch iFlex™ Flexible Current Probe	Accessory		
Wire capacity	750 MCM or 2-500 MCM		
Safety rating	CAT III 1000V, CAT IV 600V		



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa +31 (0) 40 2675 200 or
Fax +31 (0) 40 2675 222
In Canada (800)-36-FLUKE or
Fax (905) 890-6866
From other countries +1 (425) 446-5500 or
Fax +1 (425) 446-5116
Web access: <http://www.fluke.com>

©2010 Fluke Corporation.
Specifications subject to change without notice.
Printed in U.S.A. 7/2010 3801530A D-EN-N

Modification of this document is not permitted without written permission from Fluke Corporation.