

635 & 636 Series AC Hour Meters (ETI's)

- 24, 115, 220 VAC Operating voltage
- Continuous duty, rugged design
- Tamper resistant
- Permanently lubricated
- 6 Figure display: 99999.9
- Round or Square bezel mounting
- UL/cUL Approved



Square Style "Y" Bezel
Model #635 Non-resettable



Round Style "X" Bezel
Model #636 Resettable

Cramer AC Hour Meters can be found in these applications and more:



CNC Machine Tools



Waste Water Treatment



Construction Equipment



Control Panels

635 & 636 Series AC Hour Meters (ETI's)

Applications

CNC Machine
Tools



Construction Equipment



Waste Water Treatment

Control Panels



Dimensions



Model #635 Non-resettable
Round & Square Bezel




Model #636 Resettable
Round & Square Bezel

Most Popular Configurations

Model # 635		
Part #	Bezel type	Time Registration
10055	Round	HRS/TEN 115/60
10063	Square	HRS/TEN 115/60
10069	Round	MIN/TEN 115/60
10071	Round	HRS/TEN 115/60
10186	Square	HRS/TEN 115/60
30850	Square	HRS/TEN 115/60
Model # 636		
10072	Round	SEC/TEN 115/60
10074	Round	MIN/TEN 115/60
10075	Round	HRS/TEN 115/60
10080	Square	SEC/TEN 115/60
10083	Square	HRS/TEN 115/60
10086	Square	MIN/TEN 115/60

Additional configurations available.

Style "X" & "G" Bezel




(3) HOLES EQ SPACED
FOR #4 BINDING HD SCREWS.
RECOMMENDED PANEL
CUTOUT 2.22" [56.4] DIA.

Note: Style "G" Bezel is
attached to housing

Bezel Styles


Style "Y" & "K" Bezel



(4) HOLES FOR #4
PHILLIPS HD SCREWS.
RECOMMENDED PANEL
CUTOUT 2.22" [56.4] DIA.


Note: Style "K" Bezel is
attached to housing

Style "E" Bezel



(3) HOLES EQ SPACED
FOR #6 BINDING HD SCREWS.
RECOMMENDED PANEL
CUTOUT 2.82" [71.6] DIA.

Style "S" Bezel



(4) HOLES FOR #4
PHILLIPS HD SCREWS.

Specifications

Model	635	636
Display	6 Figure; 99999.9	
Time Registration	Minutes or Hours (Seconds Special Order)	Seconds, Minutes or Hours
Resettable	Not available	Push button
Motor Specification	24, 115, 220 VAC; 50 or 60hz	
Power	2.7 Watts	
Operating Temperature Range	-4°F to 131°F (-20°C to 55°C)	
Electrical Connection	6" (15 mm) Leads, 22 gauge wire	
Front Panel Mounting	3 hole Round, 4 hole Square	
Agency Approval	UL/cUL	

Options

- Bezel Style: E, X, S, or Y
- Resettable to "zero"
- Non-resettable: Recommended when tamper proofing is required to record total "on time"

www.mhrhodes.com



M.H. Rhodes Cramer Company
105 Nutmeg Road South • South Windsor, CT 06074 USA
Toll Free: 877.684.6464 • PH: 860.291.8402 • FX: 860.610.0897