






D-SUB Solder Type



Dimensions

Positions	A	B	C	D	E	F
9	30.81	24.99	16.92	16.33	11.08	19.20
15	39.14	33.32	25.50	24.66	19.39	27.70
25	53.04	47.04	38.96	38.38	33.24	41.10
37	69.32	63.50	55.42	54.84	49.86	57.30



50 Positions

D-SUB Solder Type

Material

Screwlock : Brass, 100u" min Nickel Plated.

Volatge Rating : 250 VAC/rms
60Hz

Ordering Information

1001 — □ □ □ □ □ □ □ □ □ □

0: Without core
1: With core