

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

14




R

REV PER 0G3A-0256-04



13APR04

JR

TM



## STAMPING DETAIL



- 1 FOR 7.92 [.312] MAX WIRE INSULATION DIA
- 2 SUPEREDED BY 36965
- 3 MATERIAL: BODY; COPPER PER ASTM B152  
INSULATION; PVC  
COLOR; PURPLE
- 4 FINISH: BODY; TIN PLATE PER ASTM B-545

|                                |                                |                                |
|--------------------------------|--------------------------------|--------------------------------|
| AMP<br>WIRE RANGE              | UL Listed                      | SR LR7189<br>Certified         |
| 22-10 AWG<br>SOLID OR STRANDED | 22-10 AWG<br>SOLID OR STRANDED | 22-10 AWG<br>SOLID OR STRANDED |

|        |                  |             |
|--------|------------------|-------------|
| 100    | LOOSE PC,BOX SPL | 8-36965-5   |
| 100    | LOOSE PC,BOX     | 8-36965-1   |
| 10,000 | BOXED            | 1-36965-3 2 |
| 1,500  | TAPE MOUNTED     | 1-36965-1   |
| -      | LOOSE PIECE      | 36965       |
| QTY    | DESCRIPTION      | PART NO     |


AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMSFOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER  
1-800-522-6752FOR APPLICATION  
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER  
1-800-722-1111

FOR ORDER ENTRY


1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.MAX RECOMMENDED OPERATING  
TEMPERATURE:  
90°C MAXVOLTAGE RATING:  
300V MAXCIRCULAR MIL AREA:  
1.65-6.64mm<sup>2</sup> [3248-13100]  
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
INCHES

MATERIAL

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:0 PLC ± -  
1 PLC ± -  
2 PLC ± 0.20 [.008]  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -  
FINISH

DWN G KRUPER 1/93

CHK R HERSEY 1/93

APVD M ELLIS 1/93

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco  
ElectronicsTyco Electronics Corporation  
Harrisburg, Pa 17105-3608

NAME

SPLICE, WIRE, CLOSED END

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3 00779 C-36965

SCALE 4:1

SHEET 1 OF 1

REV R