




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- SUPPLIED WITH SILVER PLATED HEX NUT AND LOCKWASHER.
- TUSONIX STANDARD PART NUMBER: 4201-050
TUSONIX RoHS COMPLIANT PART NUMBER: 4201-050 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT (Adc)	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
5,500	85°C	125 °C	10	10 G	400	10 MHz	100 MHz	1 GHz	10 GHz
	200	100				14	55	70	70

X-2015 Rev-0	REVISION RECORD			--TOLERANCES-- Unless Otherwise Specified	Title BUSHING MOUNT PI TYPE EMI FILTER		
	Original Release C.O. 970717-2						
	ADDED METRIC, DWV, IR & CIRCUIT. S.M. 01-12-04						
	20040112-2-01						
	ADDED NOTES. S.M. 07-28-05						
	20050726-2-27						
				DECIMAL ± 	Drawn S.M. 07-17-97		Scale 4 X
				ANGLES ± 	Approved T.C. 07-17-97		
				TUSONIX TUCSON, ARIZONA	A	4201-050	