






LOC FT	DIST 64	P	F	REVISIONS					
				ZONE	LTR	DESCRIPTION		DATE	APPD
					F1	RE-DISTRIBUTED		8-17-95	RT AH
					G	REV PER EC 0320-138-97		01 MAY 97	GJ

1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
- 2

TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 3

MAXIMUM DIMENSION FOR I.C. SEATING PLANE.



RECOMMENDED MOUNTING HOLE PATTERN

SCALE 4:1

OBSOLETE		BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	641856-2
	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	641856-1
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL	PART NO.

				PART NO		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON : 2 PL DEC ±-.006 3 PL DEC ±.005 ANGLES ±-.005	DR	6-11-87	 AMP INCORPORATED Harrisburg, Pa. 17105			
	M.CYRUS	6-18-87				
	CHK	R.MILLER				6-18-87
	APPD	J.LAMBERT				6-18-87
MATERIAL	APPD	SOCKET ASSY, DIP, LADDER, SHORT RET LEG, 28 POS, DIPLOMATE™ DL				
SEE TABLE	PRODUCT SPEC					
	108-1066					
FINISH	APPLICATION SPEC	SIZE	F5CM NO	DRAWING NO		
SEE TABLE	114-1049		00779	641856		
	WEIGHT	SCALE		SHEET		
	-	5:1		1 of 1		