





1 STAMP AMP 14-12* APPROX AS SHOWN




50	LOOSE PIECE, BOX	8-35684-2
5000	TAPE MOUNTED, REEL	2-35684-1
-	LOOSE PIECE	35684
QTY	PACKAGE TYPE	AMP PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 1.65-4.17mm ² [3,260-8,230] CIR MILS SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±0.20 [.008]
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL COPPER
PER ASTM B-152
ANNEALED

FINISH TIN PLATE
0.00254 [.000100] MIN
THK PER MIL-T-10727

DWN DK SCHRUM 26MAR97
CHK MJ SPICER 27MAR97
APVD JL MECKLEY 27MAR97
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE,
SOLISTRAND™

SIZE A3 CAGE CODE 00779 DRAWING NO C-35684

SCALE 5:1 SHEET 1 OF 1 REV D