

Self-Laminating Wire Marker Dispenser

- Self-laminating labels are provided in handy dispenser which protects markers when not in use
- Clear section of marker overlaminates and protects write-on legend
- Quick, easy to use for smaller installations and maintenance



Material Chart

Material	Print Method	Temperature Range	Features
Self-Laminating Vinyl, White Print-On	Pre-Printed	-40°F to 150°F (-40°C to 66°C)	Indoor/outdoor rated; thin and conformable; preferred material for most general wire/cable labeling.

Part Number	Part Description	Width		Length		Print-On Height		Min. Cable O.D.		Max. Cable O.D.		Std. Pkg.	Std. Ctn.
		In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	Qty.	Qty.
Dispenser Kit													
S100X125VARY	(1) Dispenser. (1) Roll, white write-on, vinyl label, 200/roll. (1) PFX-0 pen.	1.00	25.40	1.25	31.75	0.38	9.65	0.12	3.07	0.28	7.03	1	10
S100X225VARY	(1) Dispenser. (1) Roll, white write-on, vinyl label, 100/roll. (1) PFX-0 pen.	1.00	25.40	2.25	57.15	0.75	19.05	0.24	6.06	0.48	12.13	1	10
Refill Rolls													
S100X125VAFY	Replacement roll. White write-on, vinyl label, 200/roll.	1.00	25.40	1.25	31.75	0.38	9.65	0.12	3.07	0.28	7.03	1	10
S100X225VAFY	Replacement roll. White write-on, vinyl label 100/roll.	1.00	25.40	2.25	57.15	0.75	19.05	0.24	6.06	0.48	12.13	1	10

Can be clearly identified with Panduit permanent marking pens shown on page E5.19.

Pre-Printed Clip-On Wire Markers

- Non-adhesive markers grip tightly to wire/cable
- Markers supplied on application wand tool
- Chevron cut keeps multiple markers aligned
- Black legend is embossed into wire marker clip



Material Chart

Material	Print Method	Temperature Range	Features
Non-Adhesive Acetal	Pre-Printed	-22°F to 194°F (-30°C to 90°C)	Indoor/outdoor rated; durable material that has excellent resiliency to oils and solvents.

Part Number	Legend	No. of Markers Per Wand	Markers Per Pkg.	Std. Pkg. Qty.	Std. Ctn. Qty.
Wire/Cable Diameter 0.08" – 0.10" (2.00mm – 2.50mm)					
PCA07-A thru PCA07-Z	A thru Z	30	300	1	10
PCA07-A-J	A-J			1	10
PCA07-K-T	K-T			1	10
PCA07-U-Z	U-Z			1	10
PCA07-0 thru PCA07-9	0 thru 9			1	10
PCA07-0-9	0-9			1	10
PCA07-MIN	—			1	10
PCA07-PLS	+			1	10

Table continues on page E3.12

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index



Pre-Printed Clip-On Wire Markers (continued)

Part Number	Legend	No. of Markers Per Wand	Markers Per Pkg.	Std. Pkg. Qty.	Std. Ctn. Qty.
Wire/Cable Diameter 0.11" – 0.13" (2.80mm – 3.30mm)					
PCA11-A thru PCA11-Z	A thru Z	30	300	1	10
PCA11-A-J	A-J			1	10
PCA11-K-T	K-T			1	10
PCA11-U-Z	U-Z			1	10
PCA11-0 thru PCA11-9	0 thru 9			1	10
PCA11-0-9	0-9			1	10
PCA11-MIN	—			1	10
PCA11-PLS	+			1	10
Wire/Cable Diameter 0.13" – 0.15" (3.30mm – 3.80mm)					
PCA13-A thru PCA13-Z	A thru Z	30	300	1	10
PCA13-A-J	A-J			1	10
PCA13-K-T	K-T			1	10
PCA13-U-Z	U-Z			1	10
PCA13-0 thru PCA13-9	0 thru 9			1	10
PCA13-0-9	0-9			1	10
PCA13-MIN	—			1	10
PCA13-PLS	+			1	10
Wire/Cable Diameter 0.19" – 0.23" (4.80mm – 5.80mm)					
PCA18-A thru PCA18-Z	A thru Z	30	300	1	10
PCA18-A-J	A-J			1	10
PCA18-K-T	K-T			1	10
PCA18-U-Z	U-Z			1	10
PCA18-0 thru PCA18-9	0 thru 9			1	10
PCA18-0-9	0-9			1	10
PCA18-MIN	—			1	10
PCA18-PLS	+			1	10
Wire/Cable Diameter 0.23" – 0.37" (5.80mm – 9.40mm)					
PCA23-A thru PCA23-Z	A thru Z	20	60	1	10
PCA23-A-D	A-D		80	1	10
PCA23-E-H	E-H			1	10
PCA23-I-L	I-L			1	10
PCA23-M-P	M-P			1	10
PCA23-Q-T	Q-T			1	10
PCA23-U-X	U-X			1	10
PCA23-Y-Z	Y-Z, +, -			1	10
PCA23-0 thru PCA23-9	0 thru 9		60	1	10
PCA23-0-3	0-3		80	1	10
PCA23-4-7	4-7			1	10
PCA23-8-9	8, 9, +, -			1	10
PCA23-MIN	—		60	1	10
PCA23-PLS	+			1	10