




FEATURES:

- These SMB (Subminiature “B”) connectors snap together for quick assembly
- Connector meets interface requirements of MIL-C-39012

MATERIALS:

Body and Fittings – Brass per QQ-B-626, Alloy 360, ½ Hard

Center Contact – Brass per QQ-B-626, Alloy 360, ½ Hard

Dielectric – PTFE

Finish:

Body and Fittings – Tarnish resistant

Center Contact – Gold plated per requirements of MIL-C-39012

Marking: “POMONA 5379” located approximately as shown

RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Impedance: 50 Ohms

Frequency Range: DC to 4GHz

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

ORDERING INFORMATION: Model 5379




FIGURE #1

- Slide crimp sleeve over cable.
- Strip cable to dimensions shown.

FIGURE #2

- Slightly rotate dielectric of cable to free braid, install nut sub-assembly onto cable. Slit cable jacket if necessary.
- Push crimp sleeve against nut sub-assembly and crimp (.128 Hex).
- Solder contact to center conductor.
- Thread nut sub-assembly onto body, tighten securely

FIGURE #3

- Completed assembly shown.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA