

CATALOG LISTING

PAGE 1 OF 1

ISSUE **M**  
**8**

REPLACES PR-15555-T

CHECK

CHECK


G L H

CHECK

27 APR 87

K E W

DRAWN




**NOTES**

- 1 - UNIT INCLUDES CATALOG LISTING 1HM19 BASIC SWITCH AND JS-176 TYPE ACTUATOR, FURNISHED ASSEMBLED
- 2 - ADJUSTMENT CAUTION: DO NOT ALLOW ACTUATOR LEAF TO COME IN CONTACT WITH FIXED END OF HM LEVER, SEAL DAMAGE MAY OCCUR
- 3 - LEAF ACTUATOR ADJUSTED TO MEET SPECIFIED OPERATING POSITION PRIOR TO DELIVERY
- 4 - DISASSEMBLY, AND SUBSEQUENT REASSEMBLY MAY ALTER THIS CONDITION
- 5 - SERIAL NUMBER TO BE VISIBLE THIS AREA PER HAMILTON STD. DRG. 786126

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



| CHARACTERISTICS                    |  | ELECTRICAL DATA                |                     |                  |        | SCALE                                        | FULL  | DO NOT<br>SCALE PRINT |
|------------------------------------|--|--------------------------------|---------------------|------------------|--------|----------------------------------------------|-------|-----------------------|
| OPERATING FORCE — — — — 9 OZ MAX   |  | CONTACT ARRANGEMENT<br>S P D T |                     |                  |        | UNLESS OTHERWISE SPECIFIED<br>TOLERANCES ARE |       |                       |
| RELEASE FORCE — — — — 2 OZ MIN     |  | LOAD                           | SEA LEVEL 70,000 FT |                  |        |                                              |       |                       |
| DIFFERENTIAL TRAVEL — — — .030 MAX |  |                                | 28 VDC              | 115 VAC, 400 CPS | 28 VDC | ONE PLACE (.0)                               | ±.030 |                       |
| OVERTRAVEL — — — — .030 MIN        |  | RESISTIVE                      | 4 AMP               | 2 AMP            | 4 AMP  | TWO PLACE (.00)                              | ±.015 |                       |
|                                    |  | INDUCTIVE                      | 2 AMP               | 2 AMP            | 2 AMP  | THREE PLACE (.000)                           | ±.005 |                       |
|                                    |  | LAMP                           | 1 AMP               | .5 AMP           | 1 AMP  | ANGLES                                       | ±     |                       |
|                                    |  |                                |                     |                  |        | WEIGHT                                       |       |                       |