


Item no.: 769-610
Product description: Plug WITH CAGE CLAMP®CONNECTION FOR FREE
CONNECTION PIN SPACING 5 MM / 0.197 IN 10 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	18 (X-COM-SYSTEM)
Pin spacing from	5 mm
Pin spacing from	0.197 in
pole count	10
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	29.335 g
Color	gray
Wiring type	Front-entry
No. of connection Points	10
No. of potentials	10
Height	18.3 mm
Height	0.72 in
Width	53.6 mm
Width	2.11 in

Depth	40.2 mm
Depth	1.583 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
769-610	ABS	05-HG476175/3-PDA	500	32	4
769-610	CSA	154112-1101144	300	20	28-12
769-610	KEMA	2077750.01	500	32	4
769-610	UR	E45171	600	20	16-12
769-610	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected