

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

75018-7224

Status:


Active

Overview:

Plateau HS Dock+™ Connector System

Description:

Plateau HS Dock™ Plug, Right-Angle, 108 Circuits, Centerline Dimension 4.74mm, Lead-Free



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-45499-003 \(PDF\)](#)
- [Product Specification PS-75018-001 \(PDF\)](#)
- [Application Specification AS-75018-001 \(PDF\)](#)
- [Test Summary TS-75018-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	75018
Application	Board-to-Board, Signal
Overview	Plateau HS Dock+™ Connector System
Product Name	Plateau HS Dock™
UPC	884982686717

Physical

Breakaway	No
Circuits (Loaded)	108
Circuits (maximum)	108
Color - Resin	Black, Natural, White
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Matte Tin, Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	17.677/g
Number of Rows	3
Orientation	Right Angle
PC Tail Length	2.82mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
Packaging Type	Tray
Pitch - Mating Interface	1.50mm, 5.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
75018Series

Mates With
75019 Plateau HS Dock™ Receptacle
Right-Angle

Unmated Height	N/A
Electrical	
Current - Maximum per Contact	2.7A
Voltage - Maximum	12V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-75018-001
Product Specification	PS-45499-003, PS-75018-001
Sales Drawing	SD-75018-011
Test Summary	TS-75018-001

This document was generated on 09/05/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION