




FEATURES:

- Minigrabber® test clips attach to terminal sizes up to .060" diameter
- BNC connector is molded directly to the cable for pull strength durability and dust and moisture resistance
- Gold plated contacts for low noise connections
- Gold plated BNC center contact offers optimum corrosion resistance and low contact resistance to ensure test signal integrity

MATERIALS:

Kit contains one each Model 2449-C-48 and one each Model 3788

For full specifications, see data sheets for individual models

ORDERING INFORMATION: Model 6533

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA