



Quartz Crystal


MHz range

SMD-version

model	KX – 6
frequency	16,0 MHz
mode	fundamental
operating temperature	-10° ~ + 70°C
frequency tolerance at +25°C	± 30 ppm
temperature tolerance -10° ~ + 70°C	± 50 ppm
load capacitance C_L	12 pF
series resonance R_1 max.	100 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_O max.	5,0 pF
drive level max.	50 µW
RoHS	since production start
contents of reel	1000 pcs.
part no.	12.86525




soldering condition



(mm)

reel diameter 245 mm



suggested soldering pad