

Type BLR-I-301

Fuse Block - Indicating

For Regular Auto Blade Fuses



www.optifuse.com

(619)-593-5050

Fuse Style: Regular Auto Blade Fuses

Specifications:

Rating: 124V DC 30A

Material:

Body: Nylon (UL Flame: 94V-2)

Cap: Polycarbonate (UL Flame: 94V-2)


Terminal: Tin plated Brass – 0.25" (6.4mm) Quick Connect

Indicating: Red LED

Panel Thickness: 0.5 ~ 7.0mm

Mounting: Snap-in

Product Dimensions: Inches [mm]



Warning:



-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of Fuse Block with chemical solvent. Prolonged contact will damage the device performance.

Note: All specifications subject to change without notice.

Rev A 12/2009 - Page: 1/1
Code: S02-01H