

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301080102](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway Twin Tube 80W Fluorescent Work Light 12V, Cord Type 12/3 SOOW  
Feed Thru 1.22m (4.0') Cord Length

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374  
UL E174254

**General**

Product Family Portable Lighting  
Series [130108](#)  
NEMA Configuration Non-NEMA  
Outlet Feed-Through  
Overview [Wide-Area Lighting Products](#)  
Product Name Super-Safeway  
Type Wide Area Lamps  
UPC 78678813102

**Physical**

Cord Length - Primary 1.22m (4.0')  
Cord Length - Secondary 0.152m (6.00" )  
Depth 190.75mm (7.510")  
Duty Industrial  
Guard Included No  
Guard Type N/A  
Height 82.55mm (3.250")  
Length 636.00mm (25.039")  
Material - Globe Butyrate  
Material - Guard Nitrile Rubber 80 Shore A  
Mounting Style Adjustable Brackets  
Packaging Type Carton  
Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
Cord Type - Primary 12/3 SOOW  
Lamp Type PL-L 40/41  
Lamp Wattage - Maximum 80W  
Lumens 6300  
On/Off Switch No  
Voltage (Fixture) - Maximum 12V AC/DC

**Material Info**

Engineering Number 1052-PL12



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130108](#) Series