

CD-HF 25X60

Order No.: 3240342

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3240342>

Wiring channel, gray, halogen-free, consisting of upper and lower part,
width: 25 mm, height: 60 mm, length: 2000 mm

Commercial data

GTIN (EAN)	
sales group	B204
Pack	15 pcs.
Customs tariff	39259020
Catalog page information	Page 101 (NTK-2010)

Product notes

WEEE/RoHS-compliant since:
05/05/2009



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General**

Length (b)	2000 mm
Height	60 mm
Width (a)	25 mm
Color	gray
Base element material	ABS-PC

Inflammability class acc. to UL 94	V0
Ambient temperature (operation)	-25 °C ... 90 °C
Components	Halogen-free
Material	PC/ABS

Certificates / Approvals



Certification

CSA, UL, VDE-PZI

Accessories

Item	Designation	Description
General		
3240369	CD-HF COVER 25	Cover for wiring channel, gray, halogen-free, width: 25 mm, length: 2000 mm
3240498	RVT-PA 4	Plastic body-bound rivet, 4 mm diameter, for a material thickness of 1.5 ... 6 mm
3240499	RVT-PA 6	Plastic body-bound rivet, 6 mm diameter, for a material thickness of 1.5 ... 6 mm
1212478	UNIFOX-RVT P 4	Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets
1212509	UNIFOX-RVT P 6	Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;