

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391002008

Status:


Active

Overview:

Eurostyle™ Two-Screw Barrier Strips

Description:

10.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 8 Circuits



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                     |
|-------------------------------|-------------------------------------|
| General                       |                                     |
| Product Family                | Terminal Blocks                     |
| Series                        | 39100                               |
| Application                   | Wire-to-Wire                        |
| Component Type                | One Piece                           |
| Overview                      | Eurostyle™ Two-Screw Barrier Strips |
| Product Name                  | Eurostyle™ Two Screw                |
| Type                          | Barrier Strip                       |
| UPC                           | 78172545157                         |
| Physical                      |                                     |
| Circuits (Loaded)             | 8                                   |
| Circuits (maximum)            | 8                                   |
| Color - Resin                 | White                               |
| Entry Angle                   | Horizontal                          |
| Lock to Mating Part           | None                                |
| Material - Metal              | Stainless Steel                     |
| Material - Resin              | Nylon                               |
| Number of Rows                | 2                                   |
| Orientation                   | Vertical                            |
| PCB Retention                 | Yes                                 |
| Panel Mount                   | Mounting Holes Between Circuit      |
| Pitch - Mating Interface      | 10.00mm                             |
| Pitch - Termination Interface | 10.00mm                             |
| Polarized to Mating Part      | No                                  |
| Stackable                     | No                                  |
| Temperature Range - Operating | -40°C to +105°C                     |
| Wire Size AWG                 | 10, 12, 14, 16, 18                  |
| Electrical                    |                                     |
| Current - Maximum per Contact | 30.0A                               |
| Voltage - Maximum             | 600V                                |
| Material Info                 |                                     |
| Old Part Number               | M800-02-08-5-M1                     |
| Reference - Drawing Numbers   |                                     |
| Sales Drawing                 | SD-39100-013                        |

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION