



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	02		G2	REVISED PER ECO-14-003208	15MAR2014	NK	DR



- 1 WIRE SIZE IS #12-#10 AWG
- 2 INSULATION DIA: 3.8 - 6.4 [.15-.25]
- 3 MATERIAL THICKNESS IS 1.0 [.04]
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO END OF PIN
- 5 SUPERSEDED BY 342196-1
- 6 STAMP AMP 12-10* APPROX AS SHOWN
- 7 MAX RECOMMENDED OPERATING TEMPERATURE 105°C[221°F]

OBSOLETE	POLY BAG WITH HEADER	STANDARD	50	5 7-342196-1
	PLASTIC BOX	STANDARD	50	5 6-342196-1
	TAPED MOUNTED	STANDARD	2000	2-342196-1
	LOOSE PIECE	STANDARD	500	342196-1
	PACKAGING	LABELLING	QTY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth	07AUG03	 TE Connectivity				
		CHK T MICHIELUTTI	07AUG03					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHIELUTTI	07AUG03	NAME TERMINAL, WIRE PIN, PLASTI-GRIP,		
				PRODUCT SPEC —				
				APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL —		FINISH —		WEIGHT —				
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 of 1		REV G2