





NOTE
FACE VIEW ON
END RECEPTACLE



MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
1201140096	BTY812P-FBP-003	0.3M ± 10
1201140097	BTY812P-FBP-05	5.0M ± 25
1201140098	BTY812P-FBP-10	10.0M ± 30

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-5°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O-RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR
7	CABLE	PUR	-

DESCRIPTION EC NO: WEU2010-0451 DRWN: LSTEMMLE 2010/03/22 CHKD: NSTAUDIG APPR: FPACHER 2010/03/23	QUALITY SYMBOLS ▽ = 0 C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY LSTEMMLE	DATE 2010/03/22	MICRO-CHANGE MPIS 8 PORT PNP TWIN PORT 5P 19P MM MOULDET CONNECTOR			
		4 PLACES ± ---	± ---	CHECKED BY FP	DATE 2010/03/22					
		3 PLACES ± ---	± ---	APPROVED BY FPACHER	DATE 2010/03/23	 MOLEX INCORPORATED				
		2 PLACES ± ---	± .01	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-120114-089		SHEET NO. 1 OF 1			
		1 PLACE ± 0.3	± ---	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
		ANGULAR ± --- °								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A2							
1	REV									