



B

長蝶番

平蝶番

裏蝶番

抜差し蝶番

段付蝶番

クリーンヒンジ

特装車蝶番



フリーザーヒンジ

特殊蝶番

トルクヒンジ

ステー

周辺機器(B)

[FB-812-1-L]
サイド扉用
For side door[FB-1813-1
FB-813-1-L]
リア扉用
For rear doorFB-1813
ステンレス製FB-813・FB-812
鉄製リーフヒンジ
LEAF HINGES

FB-813-1-L



FB-1813-2-L

特徴 Feature

- 樹脂カラーを内部に組込んでいますので、回転は非常にスムーズです。
- カール部を溶接してあります。
- 中型・小型扉に最適です。
- Resin collar is incorporated in the curl so turning is very smooth.
- Curl section is welded.
- Suitable for middle- or small-sized doors.

仕様

[FB-1813] • 材質: 本体/ステンレス鋼板(SUS304)
受座/ステンレス鋼鋳物(SUS304)

• 表面仕上: 電解研磨

[FB-812] • 材質: 一般構造用圧延鋼材(SS41)

[FB-813] • 表面仕上: 垂鉛めっきクロメート処理(MFZn-C)

• 軸径: φ8

用途: 特装車・バン・船舶

納期: 標準在庫品

備考: FB-820と寸法互換です。(FB-1813・FB-813)

Specifications

[FB-1813] • Material:

Main body: Stainless steel plate (SUS304)

Base: Cast stainless steel (SUS304)

• Finish: Electrolytic polishing

[FB-813] • Material: Rolled steel for general structure (SS41)

• Finish: Zinc plating chromate treatment (MFZn-C)



• Axle diameter: φ8

Specific use: • Specially equipped vehicles, vans, ships.

Remarks: • Dimensions are almost same as FB-820.
(FB-1813, FB-813)

商品番号 Product No.	RoHS 10 2D/3D CAD	備考 Remarks	材質 Material	(L)	t	H	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price 数量 Quantity	単価 Price
FB-812-1-L	2D/3D	左型 Left-type	SPCC	/	/	/	705	61509	¥1,150	15個~	¥1,104
FB-812-1-R	2D/3D	右型 Right-type	SPCC	/	/	/	705	61503	¥1,150	15個~	¥1,104
FB-813-1-L	2D/3D	左型 Left-type	SPCC	219	6	55	820	61510	¥1,500	10個~	¥1,440
FB-813-1-R	2D/3D	右型 Right-type	SPCC	219	6	55	820	61504	¥1,500	10個~	¥1,440
FB-1813-1	2D/3D	左右兼用型 Left and right type	SUS	220	7	56	930	61121	¥5,700	5個~	¥5,480
FB-1813-2	2D/3D	左右兼用型 Left and right type	SUS	/	/	/	600	61122	¥5,600	5個~	¥5,380

●: RoHS10指令対応品 ▲: RoHS10指令に対応可能です。 ※大量のご注文は更にお安くなります。

[FB-1813-2]
サイド扉用
For side door

※本図は右扉用(左型)を示す。逆勝手は左右対称です。
※These drawings show the left type. Those of the right type is the symmetry.