

Your Location:


Part Detail:

[Connectors](#) > [D-Sub](#)

Categories

- [Cables & Adapters](#)
- [Connectors](#)
- [Custom Cable Assemblies](#)
- [Digitus Accessories](#)
- [Fiber Optics](#)
- [Heat Sinks & Fans](#)
- [Open-E NAS](#)
- [Optoelectronic](#)

Part Name:
D-Sub Connectors with
Solder Cups
Part #:
A-D-X-X-X



Contacts
Male - Brass (Male)
Female - Phosphorbronze
(Female)
Insulators
PBT, UL94V-0
Shell
Steel
Operating Temperature
-55C to +105C
Current Rating
3A

[View data sheet](#)[View data sheet](#)

Diagram

Contacts

* Click on the right side of the picture to expand or print directly.

A-D-X-X-X

1 2 3

1 - F = FEMALE | S = MALE
2 - NO. OF CONTACTS - 09,15, 25, 37, 50
3 - Version - LL - yellow chromated/contacts gold plated
LL/Z - shell tinned / contact: selective
LL/G - shell: tinned / contacts: gold plated
L-I Requirement Level I
L-II Requirement Level II

STANDARD: QUALITY CLASS III

[Home Page](#) [Privacy](#) [Product Categories](#) [Find Distributors](#) [Employment](#) [About US](#)
