

## Test adapter - PAI-4-FIX GY - 3032790

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: gray

### Your advantages

- ✓ Make contact and latch securely to any point in the function shaft
- ✓ Test adapter for accommodating safety test plugs with a 4 mm diameter



COMPLIANT

### Key Commercial Data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| Minimum order quantity               | 10 pc                                                                                                   |
| GTIN                                 | <br>4 046356 345484 |
| GTIN                                 | 4046356345484                                                                                           |
| Weight per Piece (excluding packing) | 2.200 g                                                                                                 |
| Custom tariff number                 | 85366990                                                                                                |
| Country of origin                    | Poland                                                                                                  |

### Technical data

#### Dimensions

|              |         |
|--------------|---------|
| Height       | 51.5 mm |
| Length       | 5.8 mm  |
| Width        | 5.8 mm  |
| Diameter     | 5.8 mm  |
| Pin diameter | 2.4 mm  |

#### General

# Test adapter - PAI-4-FIX GY - 3032790

## Technical data

### General

|       |                                                                                            |
|-------|--------------------------------------------------------------------------------------------|
| Note  | Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in |
|       | Do not plug in while the power is connected                                                |
|       | Latching testing accessories, therefore only suitable for being plugged in once            |
| Color | gray                                                                                       |

|                                 |                   |
|---------------------------------|-------------------|
| Material                        | Copper alloy      |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Max. voltage                    | 250 V             |
| Maximum load current            | 10 A              |
| Insertion/withdrawal cycles     | 1                 |

### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440313 |
| eCl@ss 4.0    | 27141100 |
| eCl@ss 4.1    | 27141100 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27440313 |
| eCl@ss 8.0    | 27440313 |
| eCl@ss 9.0    | 27440313 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC002255 |
| ETIM 5.0 | EC002255 |
| ETIM 6.0 | EC002255 |
| ETIM 7.0 | EC002255 |

## Test adapter - PAI-4-FIX GY - 3032790

### Classifications

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121410 |
| UNSPSC 18.0   | 39121410 |
| UNSPSC 19.0   | 39121410 |
| UNSPSC 20.0   | 39121410 |
| UNSPSC 21.0   | 39121410 |

### Approvals

#### Approvals

---

Approvals

EAC / EAC

---

Ex Approvals

---

#### Approval details

|     |                                                                                     |               |
|-----|-------------------------------------------------------------------------------------|---------------|
| EAC |  | EAC-Zulassung |
|-----|-------------------------------------------------------------------------------------|---------------|

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.BL08.B.00511 |
|-----|-------------------------------------------------------------------------------------|--------------------------|