




Model #:	Dimension "A"	Dimension "B"	Accepts Wire AWG:
4934	.062" (1.57mm)	.160" (4.06mm)	18, 20, 22
4987	.120" (3.05mm)	.200" (5.08mm)	14, 16

- Threaded two piece design allows wires to be soldered or crimped to the banana jack body.
- Heavy-duty plastic body withstands cracking if accidentally dropped.
- Fits into Pomona Models 4933 & 4986 Banana Plugs.

MATERIALS:

Banana Jack: Body – Brass, Nickel Plated

Insulation: Nylon, Color per part number

Threaded Handle: Nylon, Color per part number, Marking: "POMONA ELECT." & Part Number

RATINGS:

Operating Voltage: 1,200 Volts (AC/DC)

Current: 15 Amps Max.

Operating Temperature: +80°C (+176°F)

ORDERING INFORMATION: 4934-* or 4987-*

* = Color Code, Standard Colors: -0 Black, -2 Red

All dimensions are in Inches (Millimeters). Tolerances (except as noted): .xx = ±.02" (.51mm), .xxx ± .005" (.127mm)

All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4934-0](#) [4934-2](#)