

APAX-5520CE/KW APAX-5620CE/KW

PAC with Marvel XScale® CPU

PAC with Marvel XScale® CPU and CAN



APAX-5520CE/KW



Specifications

General

- **Certification** CE, FCC class A
- **Dimensions (W x H x D)** 30 x 139 x 100 mm
- **Enclosure** ABS+PC
- **Weight** 210 g
- **Power Consumption** 4.5 W @ 24 V_{DC} (typical)

System Hardware

- **CPU** Intel XScale PXA270 520 MHz
- **Memory Flash** 32M bytes, SDRAM 64M bytes
- **Battery Backup Memory** 256 KB file system, 256 KB direct access
- **Real-time Clock** Yes
- **Watchdog Timer** Yes
- **VGA** DB15 connector
- **SB Ports** 1 x USB 1.1
- **Storage** 1 x Type II CompactFlash card slot

Software

- **OS Support** Windows CE
- **Control Software** C/C++ and .NET library
KW Multiprog (development tool)
KW ProConOS (runtime kernel)

I/O Expansion

- **Connected I/O Modules** 32 (max.)*
- **Digital Signals** 768 (max.)
- **Analog Signals** 192 (max.)

Communication (Ethernet)

- **LAN Ports** 1 x RJ-45 Port, 10/100 Mbps
- **Offers Modbus/TCP Server and Client APIs**

Communication (Serial)

- **Medium** 1 x Isolated RS-485 (2-wire, isolated)
- **Offers Modbus/RTU Master and Slave APIs**

Environment

- **Operating Temperature** -10 ~ 55°C (when mounted vertically)
- **Storage Temperature** -40 ~ 70°C
- **Relative Humidity** 5 ~ 95% (non-condensing)

Ordering Information

- **APAX-5520CE** PAC with Marvel XScale CPU, WinCE
- **APAX-5520KW** PAC with Marvel XScale CPU, KW

Accessories

- **APAX-5002** 2-slot Backplane Module
- **APAX-5343E** Power Supply for APAX Expansion Module

*APAX DI/O modules can use ID number 0 ~ 31, while AI/O modules and counter modules can only use ID numbers 0 ~ 15

NEW



APAX-5620CE/KW



Specifications

General

- **Certification** CE, FCC class A
- **Dimensions (W x H x D)** 60 x 139 x 100 mm
- **Enclosure** ABS+PC
- **Weight** 310 g
- **Power Consumption** 5 W @ 24 V_{DC} (typical)
- **Redundancy** 25ms data sync, 20ms changeover time and 14kbytes for data sync

System Hardware

- **CPU** Marvel XScale PXA270 520 MHz
- **Memory Flash** 32M bytes, SDRAM 64M bytes
- **Battery Backup Memory** 256 KB file system, 256 KB direct access
- **Real-time Clock** Yes
- **Watchdog Timer** Yes
- **VGA** DB15 connector
- **USB Ports** 1 x USB 1.1
- **Storage** 1 x Type II CompactFlash card slot

Software

- **OS Support** Windows CE
- **Control Software** C/C++ and .NET library
KW Multiprog (development tool), KW ProConOS (runtime kernel)

I/O Expansion

- **Connected I/O Modules** 32 (max.)*
- **Digital Signals** 768 (max.)
- **Analog Signals** 192 (max.)

Communication (Ethernet)

- **LAN** 2 x RJ-45 Port, 10/100 Mbps
- **Offers Modbus/TCP Server and Client APIs**
- **Modbus/TCP under KW** Server : 64 connections
Client : 128 connections

Communication (Serial)

- **Medium** 2 x Isolated RS-485 (2-wire, isolated, max. distance 4,000 ft)
- **Offers Modbus/RTU Master and Slave APIs**

Communication (CAN)

- **Medium** 2 x Isolated CAN
- **Protocol** CANopen (DS301/302)
- **Speed maximum** 1 Mbit/s

Environment

- **Operating Temperature** -10 ~ 55°C (when mounted vertically)
- **Storage Temperature** -40 ~ 70°C
- **Relative Humidity** 5 ~ 95% (non-condensing)

Ordering Information

- **APAX-5620CE** PAC with Marvel XScale CPU, CAN, WinCE
- **APAX-5620KW** PAC with Marvel XScale CPU, CAN, KW

Accessories

- **APAX-5002** 2-slot Backplane Module
- **APAX-5343E** Power Supply for APAX Expansion Module