

Wiha TorqueControl Blades - For Easy Torque, TorqueFix & TorqueVario Handles



285 Slotted Interchangeable Blades For TorqueFix & TorqueVario

Slotted tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item					Max. Torque		
No.	mm	Inch	mm	lbs.	Nm	pkg.	
285 34	1.5	.059	175	.07	0.15	1	
285 35	2.0	.078	175	.07	0.4	1	
285 36	2.5	.098	175	.07	0.4	1	
285 37	3.0	.118	175	.07	0.6	1	
285 38	3.5	.139	175	.07	1.1	1	
285 39	4.0	.157	175	.07	2.5	1	



285 Phillips Interchangeable Blades For TorqueFix & TorqueVario

Phillips tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item					Max. Torque		
No.	Size	mm	mm	lbs.	Nm	pkg.	
285 40	000	175	4.0	.07	0.4	1	
285 41	00	175	4.0	.07	0.4	1	
285 42	0	175	4.0	.07	0.4	1	
285 43	1	175	4.0	.07	3.8	1	



285 TORX® Interchangeable Blades For TorqueFix & TorqueVario

TORX® tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item					Max. Torque		
No.	Size	mm	mm	lbs.	Nm	pkg.	
285 61	T5	175	4.0	.07	0.4	1	
285 62	T6	175	4.0	.07	0.6	1	
285 63	T7	175	4.0	.07	0.9	1	
285 64	T8	175	4.0	.07	1.3	1	
285 65	T9	175	4.0	.07	2.5	1	
285 66	T10	175	4.0	.07	3.8	1	
285 67	T15	175	4.0	.07	5.5	1	
285 68	T20	175	4.0	.07	8.0	1	
285 69	T25	175	4.0	.07	8.0	1	



285 TORX® Plus® Blades For TorqueFix & TorqueVario

TORX® Plus® tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item					Max. Torque		
No.	Size	mm	mm	lbs.	Nm	pkg.	
285 71	IP5	175	4.0	.07	0.5	1	
285 72	IP6	175	4.0	.07	0.8	1	
285 73	IP7	175	4.0	.07	1.3	1	
285 74	IP8	175	4.0	.07	2.0	1	
285 75	IP9	175	4.0	.07	3.0	1	
285 76	IP10	175	4.0	.07	4.5	1	
285 77	IP15	175	4.0	.07	6.6	1	
285 78	IP20	175	4.0	.07	8.0	1	
285 79	IP25	175	4.0	.07	8.0	1	



285 Hex Metric Interchangeable Blades For TorqueFix &

TorqueVario Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max. Torque		
No.	mm	mm	lbs.	Nm	pkg.	
285 45	1.5	175	.07	0.9	1	
285 46	2.0	175	.07	1.8	1	
285 47	2.5	175	.07	3.8	1	
285 48	3.0	175	.07	8.0	1	
285 49	4.0	175	.07	8.0	1	



285 Hex Inch Interchangeable Blades For TorqueFix &

TorqueVario Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max. Torque		
No.	Inch	mm	lbs.	Nm	pkg.	
285 55	.050	175	.07	.3	1	
285 56	1/16	175	.07	.5	1	
285 57	5/64	175	.07	.6	1	
285 58	3/32	175	.07	1.3	1	
285 59	7/64	175	.07	2.5	1	
285 60	1/8	175	.07	3.8	1	
285 87	9/64	175	.07	8.0	1	
285 88	5/32	175	.07	8.0	1	



285 MagicSpring TORX® Interchangeable Blades For TorqueFix

& **TorqueVario** blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max. Torque		
No.	Size	mm	mm	lbs.	Nm	pkg.
285 12	T6	175	4.0	.07	0.6	1
285 27	T7	175	4.0	.07	0.9	1
285 28	T8	175	4.0	.07	1.3	1
285 29	T9	175	4.0	.07	2.5	1
285 30	T10	175	4.0	.07	3.8	1
285 31	T15	175	4.0	.07	5.5	1
285 32	T20	175	4.0	.07	8.0	1
285 33	T25	175	4.0	.07	8.0	1



Screw
Holding



286 MagicSpring TORX® Plus® Interchangeable Blades For

TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts.

High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max. Torque		
No.	Size	mm	mm	lbs.	Nm	pkg.
286 11	IP6	175	4.0	.07	0.8	1
286 12	IP7	175	4.0	.07	1.3	1
286 13	IP8	175	4.0	.07	2.0	1
286 14	IP9	175	4.0	.07	3.0	1
286 16	IP10	175	4.0	.07	4.5	1
286 17	IP15	175	4.0	.07	6.6	1
286 18	IP20	175	4.0	.07	8.0	1
286 19	IP25	175	4.0	.07	8.0	1



Screw
Holding

*None of the blades featured on this page will function in a TorqueVario Insulated Handle