


G4010 series



Size: (40 x 40 x 10.3 mm)
1.57 x 1.57 x 0.41 inches

Construction: UL94V-0 impeller & frame


Bearing option: ball bearing

Connection: AWG 26, UL1061 lead wires

Frame: ribbed

Protection: thermal

Options: tachometer output or locked rotor alarm signal



Model No.	Rated Voltage V	Current mA			Revolution RPM	Air Volume		Max. Static Pressure (H ₂ O)		Sound Noise dbA	Weight g
		5	12	24		M³/Min.	CFM	MM	INCH		
G4010S	5/12	90	60	-	4,000	0.12	4.2	1.20	0.05	21	18
G4010L	5/12	140	100	-	5,000	0.16	5.6	2.70	0.11	24	18
G4010M	5/12	240	150	-	6,000	0.19	6.7	3.70	0.15	28	18
G4010H	5/12/24	400	220	160	8,000	0.25	8.8	6.40	0.25	35	18
G4010E	12/24	-	350	250	10,000	0.32	11.3	9.90	0.39	41	18