


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	8/17/01	TJC
B	ECN3264: CN RELEASE	04/01/08	D. PARHAM
C	ECN 3779: DEFINED COLOR TO LIGHT GRAY, NEW FORMAT	1/13/09	D.FRISIELLO
.	.	.	.



WIRING MAP		
"P1"	COLOR	"P2"
1	BROWN	1
2	RED	2
3	ORANGE	3
4	YELLOW	4
5	GREEN	5
6	BLUE	6
7	VIOLET	7
8	GRAY	8
9	WHITE	9
10	LIGHT GREEN	10
11	BLACK	11
12	GRAY/BLACK	12
13	BLUE/WHITE	13
14	VIOLET/WHITE	14
15	BROWN/WHITE	15
16	BLACK/WHITE	16
17	RED/WHITE	17
18	ORANGE/WHITE	18
19	GREEN/WHITE	19
20	GRAY/GREEN	20
21	GRAY/RED	21
22	GRAY/VIOLET	22
23	LIGHT GREEN/BLACK	23
24	RED/BLACK	24
25	ORANGE/BLACK	25
26	YELLOW/BLACK	26
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CHD26MF-2.5	2.5	0.76
CHD26MF-5	5.0	1.52
CHD26MF-10	10.0	3.05
CHD26MF-15	15.0	4.57
CHD26MF-25	25.0	7.62
CHD26MF-50	50.0	15.24

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVALS		DATE		 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC		8/15/01			
	CHECKED BY DFP		8/15/01			
	APPROVED BY RC		8/17/01			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				CATEGORY DATA CABLING	
	PRODUCT DESCRIPTION HD26M TO HD26F DATA CABLE ASSEMBLY					
PROJECTION	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. CHD26MF	REV. C
	CHD-FS01		SCALE: NONE	CAD FILE: CHD26MF.SLDDRW		SHEET 1 OF 1