





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CFPTR2B**	2.59 LB/10 PCS (1174.1 g/10 PCS)


NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PARTS INCLUDED:
 - 2- MOUNTING SCREW #6-32 X 1" (SECURES FACEPLATE TO WALL)
 - 2- TAMPER RESISTANT SCREW HEX BUTTON HEAD #6-32 X 1.25" (SECURES COVER TO BASE)
 - 1- BASE
 - 1- COVER
 - 2- COVER SCREW #6-32 X 1.25" COMBINATION PAN HEAD (SECURES COVER TO BASE)



MODEL FILENAME	MO1445AA_CFPTR2B_ASMBLY_02.PRT	SIZE
DRAWING FILENAME	MO1445AA_DC_02A.PRT	A

MINI-COM™ TAMPER RESISTANT FACEPLATE
WITH 2 BREAKOUT PORTS CUSTOMER DRAWING

 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	N/A
	PRODUCT SPEC	N/A
	WORK INSTRUCTION	N/A
	SCALE	FULL
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.	
	DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	
	REVIEW DRAWING NUMBERS	
DRAWN BY JsP	PART NO. CFPTR2B**	
DATE 12-15-04	DRAWING NO. 01445-02	
CHK'D	SHEET 1 OF 2	

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH
R	12-15-04	JsP		RELEASED TO PRODUCTION	01445-02					

