



5.0V HCMOS TRI-STATE ENABLE/DISABLE OSCILLATORS

MODEL: F5C-2E

FEATURES

- 5.0V Operation
- HCMOS/TTL Output
- Tri-State Enable/Disable
- 14-Pin DIP

OPTIONS

- 8-Pin DIP Available (H5C-2E)



Discontinued

Learn more about:

[Part Marking Identification](#)

[Mechanical Specification](#)

Internet required



• PART NUMBER SELECTION [Learn More - Internet Required](#)

Part Number	Model Number	Frequency Stability ¹	Operating Temperature (°C)	Frequency Range (MHz)
147-Frequency-xxxxx	F5C-2E	±100PPM	0 ~ +70	1.000 ~ 160.000
326-Frequency-xxxxx	F5C-2ER	±100PPM	-40 ~ +85	1.000 ~ 160.000
180-Frequency-xxxxx	F6C-2E	±50PPM	0 ~ +70	1.000 ~ 160.000
181-Frequency-xxxxx	F6C-2ER	±50PPM	-40 ~ +85	1.000 ~ 160.000
199-Frequency-xxxxx	F7C-2E	±25PPM	0 ~ +70	1.000 ~ 160.000
330-Frequency-xxxxx	F7C-2ER	±25PPM	-40 ~ +85	1.000 ~ 125.000
513-Frequency-xxxxx	F8C-2E	±20PPM	0 ~ +70	1.000 ~ 125.000




• ELECTRICAL CHARACTERISTICS

PARAMETERS	MAX (unless otherwise noted)
Frequency Range (Fo)	1.000 ~ 160.000 MHz
Storage Temperature Range (Tstg)	-55°C ~ +125°C
Supply Voltage (VDD)	5.0V ± 10%
Input Current (IDD)	
1.000 ~ 40.000 MHz	40mA
40.000+ ~ 125.000 MHz	60mA
125.000+ ~ 160.000 MHz	100mA
Output Symmetry (50% VDD)	
1.000 ~ 50.000 MHz	45% ~ 55%
50.000+ ~ 160.000 MHz	40% ~ 60%
Rise Time (10% ~ 90% VDD) (Tr)	
1.000 ~ 125.000 MHz	10 nS
125.000+ ~ 160.000 MHz	6 nS
Fall Time (90% ~ 10% VDD) (Tf)	
1.000 ~ 125.000 MHz	10 nS
125.000+ ~ 160.000 MHz	6 nS
Output Voltage (VOL)	10% VDD
(VOH)	90% VDD Min
Output Current (IOL)	16mA Min
(IOH)	-16mA Min
Output Load	
TTL	10TTL
HCMOS	50pF
Start-up Time (Ts)	10mS
Output Enable/Disable Time ²	100nS

¹ Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock, and vibration.

² An internal pullup resistor from pin 1 to VDD allows active output if pin 1 is left open.

All specifications subject to change without notice. Rev. 6/1/04



Pin Connections

#1 E/D #7 GND (Case) #8 Output #14 Vdd

All dimensions are in millimeters.

• ENABLE / DISABLE FUNCTION

INH (Pin 1)	OUTPUT (Pin 8)
OPEN ²	ACTIVE
'1' Level VIH ≥ 2.2 V	ACTIVE
'0' Level VIL ≤ 0.8 V	High Z