



LR55 Series Releasable Ties

Features and Benefits


The extended pawl allows for quick and simple release of the ties. Manufactured in various colours these cable ties are ideal for applications where colour coding is required. Additionally, the LR55 Series are outside serrated, minimising the risk of damage to cable insulation.

Application





These releasable and reusable ties are ideal where temporary installation or the addition or removal of cables is required, for example: logistic identification (colour coding), packaging industries, cable harness manufacturing.



The LR55 cable ties are reusable and ideal for colour coding.



LR55 Series

Material Data	
Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2
 	
Material Data	
Material	Polyamide 6.6 Heat Stabilised (PA66HS)
Operating Temperature	-40 °C to +105 °C Continuous, (+145 °C for 500 h)
Flammability	UL94 V2
 	

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour
LR55S							
115-00010	LR55S	145	4.7	35.0	245	PA66	Red (RD)
115-00011	LR55S	145	4.7	35.0	245	PA66	Yellow (YE)
115-00012	LR55S	145	4.7	35.0	245	PA66	Green (GN)
115-00013	LR55S	145	4.7	35.0	245	PA66	Blue (BU)
115-00014	LR55S	145	4.7	35.0	245	PA66	Grey (GY)
115-00015	LR55S	145	4.7	35.0	245	PA66	Natural (NA)
115-00009	LR55S	145	4.7	35.0	245	PA66HS	Black (BK)
LR55R							
115-00003	LR55R	195	4.7	50.0	245	PA66	Red (RD)
115-00004	LR55R	195	4.7	50.0	245	PA66	Yellow (YE)
115-00005	LR55R	195	4.7	50.0	245	PA66	Green (GN)
115-00006	LR55R	195	4.7	50.0	245	PA66	Blue (BU)
115-00007	LR55R	195	4.7	50.0	245	PA66	Grey (GY)
115-00008	LR55R	195	4.7	50.0	245	PA66	Natural (NA)
115-00002	LR55R	195	4.7	50.0	245	PA66HS	Black (BK)

All dimensions in mm. Subject to technical changes.