





- NOTES:
- INSULATOR MATERIAL: PBT.
 - CONTACT MATERIAL: PHOSPHOR BRONZE.
 - PLATING: SEE PART NUMBER CODING.
 - OPERATING TEMPERATURE: -40°C TO +85°C.
 - UL FLAMMABILITY RATING: 94V-0.
 - CURRENT RATING: 1 AMP PER CONTACT..
 - INSULATION RESISTANCE: 1,000M OHMS MIN.
 - DIELECTRIC WITHSTANDING: 500 VAC R.M.S. FOR ONE MINUTE.
 - CONTACT RESISTANCE: 30m OHMS MAX.
 - MATES WITH SBH41 SERIES.
 - FOR FLAT CABLE CONNECTOR, WITH STRAIN RELIEF.



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES[MM]
TOLERANCES:
ANGULAR: ± 30'
.XX = ± .012 [.30]
.XXX = ± .008 [.20]
.XXXX = ± .004 [.10]
SURFACE FINISH: 63 Ra
REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING PER: ANSI Y14.5M-1994

		DATE	NAME		SULLINS CONNECTOR SOLUTIONS
DRAWN	11/06/08	JH			
THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.					DESCRIPTION HEADER FEMALE, .050X.100[1.27X2.54] CC, SR
					PART NUMBER SFH413-PP_B-D_-ID-_-
	SIZE		DWG. NO.		REV
	C		11164		C
SCALE: NTS					SHEET 1 OF 1