




LOC		DIST		REVISIONS						
GP		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
			A	REVISED PER EC 0S13-0266-05				18JUL06	BM	CR



ASSEMBLED VIEW



- CONTACTS ACCEPT 20-24 AWG RANGE.
- INSERTS: NYLON, GLASS FILLED, UL 94V-0 RATED, BLACK.
- CABLE CLAMPS: POLYPROPYLENE, BLACK
- CONTACTS: BRASS.
- SHELLS: CARBON STEEL.
- CABLE GATE PLUG TO BE PLACED IN CABLE EXIT NOT BEING USED.
- CONTACTS: GOLD FLASH FOR A LENGTH OF 3.81[.150] MIN FROM MATING END, 2.54µm[.000100] MIN TIN ON OPPOSITE END FOR A LENGTH OF 4.06 [.160] MIN FROM END OF INSULATION BARREL, BOTH OVER 0.76µm[.000030] MIN NICKEL ON ENTIRE CONTACT.
- SHELLS: 5.08µm[.000200] MIN TIN OVER 2.54µm[.000100] MIN COPPER.
- STRAIN RELIEF CLIP CAN BE REVERSED FOR PROPER INSTALLATION, DEPENDING ON SIZE OF CABLE DIAMETER.
- STRAIN RELIEF CLIP AND SELF TAPPING SCREWS MAY BE USED AT EITHER CABLE EXIT.

11. CABLE DIAMETER RANGE = 4.58-11.68 [.180-.460].

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. REITZEL CHK S. BOLASH APVD M. WAMSLEY	1AUG03 1AUG03 1AUG03	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		± - ± - ± 0.13[.005] ± - ± - ± -		PRODUCT SPEC 108-40005 APPLICATION SPEC 114-40030	
MATERIAL		FINISH		SIZE A1	CAGE CODE 00779
2/3/4/5		7/8		DRAWING NO 749808-7	
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 of 1	
				REV A	