


SRSL 10-T35



Tightening torque/thread 2.0 Nm/M 4 Inspection Test Pattern Size A 5

Type Cat.-No. Qty.p.pck.
SRSL 10-T35 41213.2 green/yellow 80

Ratings:

Dimensions TS 35
 LxBxH (mm) 56x10x47
 Stripped Length 12 mm

Max Rated Cross Section

Single Wire (solid) 0.2-10 mm²
 Stranded Wire (flexible) 0.2-10 mm²
 Wire Size AWG 20-8

SRSL 16-T32



Tightening torque/thread 4.0 Nm/M 5 Inspection Test Pattern Size B 7

Type Cat.-No. Qty.p.pck.
SRSL 16-T32 41196.2 green/yellow 50

Ratings:


Dimensions TS 32
 LxBxH (mm) 50x12x63
 Stripped Length 12 mm

Max Rated Cross Section

Single Wire (solid) 2.5-25 mm²
 Stranded Wire (flexible) 2.5-16 mm²
 Wire Size AWG 12-6

EARTH TERMINAL BLOCKS

SRSL 35-T32



Tightening torque/thread 5.0 Nm/M 6 Inspection Test Pattern Size B 8

Type Cat.-No. Qty.p.pck.
SRSL 35-T32 41198.2 green/yellow 20

Ratings:

Dimensions TS 32
 LxBxH (mm) 58x16x76
 Stripped Length 20 mm

Max Rated Cross Section

Single Wire (solid) 2.5-50 mm²
 Stranded Wire (flexible) 2.5-35 mm²
 Wire Size AWG 12-2

SRSL 16-T35



Tightening torque/thread 4.0 Nm/M 5 Inspection Test Pattern Size B 7

Type Cat.-No. Qty.p.pck.
SRSL 16-T35 41197.2 green/yellow 50

Ratings:

Dimensions TS 35
 LxBxH (mm) 56x12x58
 Stripped Length 12 mm

Max Rated Cross Section

Single Wire (solid) 2.5-25 mm²
 Stranded Wire (flexible) 2.5-16 mm²
 Wire Size AWG 12-6