



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	SEE DETAIL	MATERIAL	"A" +/- .062	"B" +/- .062	INSIDE NOMINAL DIA.	MIN ID SUPPLIED	MAX. RECOVERED	MARKER ACROSS	TUBING COLOR	PKG. QTY.	SEE STYLE
H100X165HST-2	B	GMUFR31	1.00 [25.4]	3.50 [88.9]	1.00 in. [25.4 mm]	1.00 in. [25.4 mm]	0.315 [8.0]	2	YELLOW	500	A
H200X165HST-2	A		2.00 [50.8]					1		250	



										PANDUIT CORP. TINLEY PARK, ILLINOIS				
										CUSTOMER DRAWING H***X165H*T-2 TWO-SIDED HEAT SHRINK LABEL FLUID RESISTANT				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (,XXX) ± .020 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY RVU	MAT'L: HEAT SHRINK TUBING, GMUHF21		SCALE NTS	
O	12/13/11	RVU		DRAWING RELEASE.	6566	R				DATE 11/14/11			DRAWING NO. C10962	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D He/la			SIZE	