


Dimensions: mm (In.)

**Mechanical Specifications:**

- Operating Frequency: 240 operations/min
- Life: 10,000,000 operations min.

Electrical Specifications:

- Rating: 5A/125VAC/250VAC
- Insulation Resistance (at 500VDC): 100M Ω min.
- Dielectric Strength: 1,000VAC RMS (50-60HZ)
- Operating Frequency: 20 operations/min
- Life: 100,000 operations min.
- Inrush: NC: 15A; NO: 7A

Operating Characteristics:

- Operating torque (OT): 7.6g-cm max.
- Releasing torque (RT): 0.9g-cm min.
- Pretravel (PT): 21° max.
- Overtravel (OT): 17° min.
- Movement differential (MD): 2° min.
- Return travel (RT): 5° min.
- Total travel (TT): 38° min.
- Free position (FP): 15 $\pm$ 3°

Snap Switches

SNS51-05-7P6ST-S01, SNS51-05-7P6B1-S01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-51-05-7P6ST-S01](#) [101-51-05-7P6B1-S01](#)