

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0745264150

Status:

Active

Overview:

lanelink

Description:

0.50mm (.020") Pitch LaneLink™ 10Gbase-CX4 Cable Assembly, 24 AWG, Lanyard Latch, 15.0m (49.21') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Cable Assemblies

Series

74526

Connector to Connector

4X Plug-to-4X Plug

Overview

lanelink

Product Name

10Gbase-CX4, 4X, LaneLink™

Physical

Cable Length

15.0m (49.21')

Circuits (Loaded)

16

Gender

Plug/Plug

Lock to Mating Part

Yes

Packaging Type

Bag

Single Ended

No

Waterproof / Dustproof

No

Wire Insulation Diameter

N/A

Wire Size AWG

24

Wire/Cable Type

Round

Electrical

Current - Maximum per Contact

0.5A

Impedance

100#

Shield Type

Full Shield

Shielded

Yes

Voltage - Maximum

30V AC

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-74526-400



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74526Series

Mates With

91525 4X/12X Latch LaneLink™ Receptacle. 91804 LaneLink™ Connector

Use With

74735 X2 Transceiver. 74739 XPAK Transceiver

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION