



REV.	DATE	ECR NO.	DESCRIPTION
NC	03/23/11	XXXXXX	INITIAL RELEASE



1. FREQUENCY RANGE: DC 0–26.5 GHZ

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE	Amphenol Connex PART DESCRIPTION SMP BULLET ADAPTOR JACK TO JACK PART NO. 302101 DWG. NO. 122532RP.DWG REV. NC SIZE A SCALE NA			
	DRAWN	S.LI	03/23/11				
	CHECKED						
	ISSUED						
	SHEET	1 OF 1					
				CAD FILE	C:/CONNEX/302101.DWG		

3	CONTACT PIN	BERYLLIUM COPPER	GOLD	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	BERYLLIUM COPPER	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY