

SPARE HANDSET & CHARGER



Packing

1 Charger
1 Handset

1 Adapter
3 AAA-NiMh batteries

Technical Data

Standard: DECT (Digital Enhanced Cordless Telecommunications)
GAP (Generic Access Profile)

Frequency range:

1880 ~ 1900 MHz (BW=20MHz)

1920 ~ 1940 MHz (BW=20MHz)

RF channels: 10 channels

Channel Bandwidth: 1.728

Modulation: GFSK

Transmission Output Power: 10mW

Antenna diversity supported Base Station

Data Transmission Rate: 1.152 Mbps

Speech coding: ADPCM 32 K bps

Communication Range (max.):

Outdoor - 300 Meters

Indoor - 50 Meters

Power Supply

Base Station Adapter: INPUT AC110 / 230 VAC 60Hz / 50Hz

OUTPUT DC 9V 350mA

Charger Adapter: INPUT AC110 / 230 VAC 60Hz / 50Hz

OUTPUT DC 7,5V 210mA

Handset: Ni-MH Rechargeable Battery 1,2V AAA*3

Operating Time: Standby 200 Hours - Talk: 18 Hours

Operating Temperature: 0°C to 40°C

Storage Temperature: 0°C to 40°C

Dimensions

Handset: 135 x 51 x 29 mm L/W/D

Base Station: 179 x 141 x 42 mm L/W/D

Charger: 80 x 60 x 110 mm L/W/D

Weight

Base station: 400g (approx.)

Handset: 150g (approx.)

Charger: 80g (approx.)