



MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING
914CE3-6AK




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - NEMA 1, 3, 4, 12 AND 13 SEALING
- 3 - SIDE EXIT CABLE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 2.7 LB MAX
RELEASE FORCE — — — — 1.0 LB MIN
DIFFERENTIAL TRAVEL — — — .004 MAX
OVERTRAVEL — — — — — .118 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A - 250 VAC
1/10HP - 125 OR 250 VAC



SCALE FULL

DO NOT
SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT

914CE3-6AK

M

DRAWING
NUMBER

2

ISSUE

REVISIONS
A CO-
69061
S A V
4 OCT 91

DDM/CAD

DRAWN

REPLACES

PR-17647

CHECK

CHECK

14 NOV 91

14 NOV 91

CHECK

14 OCT 91