



1060

Micro

From small sensitive components to smartphones, protect your gear from the elements in a crushproof, watertight, & dustproof Micro Case from Pelican.

- ***Case is able to be submerged under 1 meter of water for up to 30 minutes in accordance with IP67 testing parameters**
- **Available in clear with color liner or solid**
- **Watertight, crushproof, and dustproof**
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Carabiner
- Easy open latch
- Lifetime Guarantee of Excellence
- Rubber liner for extra protection doubles as o-ring seal
- Stainless steel hardware



DIMENSIONS

Interior (LxWxD)	8.25 x 4.25" x 2.25 (21 x 10.8 x 5.7 cm)
Exterior (LxWxD)	9.88 x 5.59" x 2.63 (25.1 x 14.2 x 6.7 cm)
Lid Depth	0.69" (1.8 cm)
Bottom Depth	1.44" (3.7 cm)
Total Depth	2.13" (5.4 cm)
Int Volume	0.05 ft ³ (0.001 m ³)

MATERIALS

Body	Polycarbonate (PC)
Latch	Xylex
O-Ring	Thermoplastic Rubber
Pins	Stainless Steel
Foam	TL - 426 4 lb. Esther
Purge Body	Polycarbonate (PC)
Purge Vent	Polyester Spun-Bond ePTFE Oleophobic

COLOURS

 Black	 OD Green	 Yellow	 Tan
 Seafoam	 Black - Clear	 Yellow - Clear	 Blue - Clear
 Red - Clear	 Indigo	 Bright Green	 Oxblood

WEIGHT

Weight With Foam	1.03 lbs (0.5 kg)
Weight Empty	1.00 lbs (0.5 kg)
Buoyancy	2.49 lbs (1.1 kg)
Master Pack Weight	7.08 lbs (3.2 kg)

TEMPERATURE

Minimum Temperature	-10°F (-23.3 °C)
----------------------------	------------------

Maximum Temperature 199°F (92.8 °C)

CERTIFICATIONS

IP67

FOAM PROPERTIES

Layer 1 (Lid)	0.13" Pad
Layer 2 (Base)	1.43" Pick N Pluck

OTHER

Minimum Pack	6
Master Pack	6
Military	yes

ACCESSORIES



1061
Replacement Case Liner



1062
Pick N Pluck™ Foam Insert

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 10-03-20