


NOTES:


1. HARDWARE IS INCLUDED.



LEAD FINISH:	SOLDER
BUSHING FINISH:	SILVER
CAPACITANCE	.027uF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C N/A VDC MAX. 125°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	

FREQ. MHz	I.L. (db)
1	10
10	30
100	50
200	--
1 GHz	70
10 GHz	70

SCHEMATIC



MARKING:

PART: S000

BAG:

SCI-3112-000

DATE CODE

LOT NO.

QTY/BAG (200 MAX.)

03	02	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED
CN. 203433	CN. 169173	CHANGE NOTICE	Fractions ± 1/64
			Dec. .xx±
			Dec. .xxx±.010
			Angles ±0° 30'
			CODE IDENT. NO. DLSP2



SPECTRUM CONTROL INC.

ERIE, FAIRVIEW
PENNSYLVANIA

Dwn. KAUFFMAN

Ckd. 8/28/01

Apvd.

Scale NONE

Description L
RESIN SEAL FILTER

SCI-3112-000