










		BEIGE (726C)	15μ"	2-1734309-8
		BLACK (426C)	15μ"	2-1734309-7
OBSOLETE		BEIGE (726C)	30μ"	2-1734309-6
		BLACK (426C)	30μ"	2-1734309-5
OBSOLETE	2.84	BEIGE (726C)	5μ"	2-1734309-4
OBSOLETE		BLACK (426C)	5μ"	2-1734309-3
OBSOLETE		BEIGE (726C)	G/F	2-1734309-2
OBSOLETE		BLACK (426C)	G/F	2-1734309-1
		BEIGE (726C)	15μ"	1734309-8
		BLACK (426C)	15μ"	1734309-7
		BEIGE (726C)	30μ"	1734309-6
		BLACK (426C)	30μ"	1734309-5
		BEIGE (726C)	5μ"	1734309-4
		BLACK (426C)	5μ"	1734309-3
		BEIGE (726C)	G/F	1734309-2
		BLACK (426C)	G/F	1734309-1
		Housing Color	Min. Gold Thickness	Part Number
	DIM A			

WITH SPRING



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
MM			
		0 PLC	± .
		1 PLC	± .30
		2 PLC	± .25
		3 PLC	± .20
		4 PLC	± .
		ANGLES	± 3'
MATERIAL	FINISH		
SEE NOTE		SEE NOTE	

DWN B. HSING	06FEB2009	 TE Connectivity	
CHK S. CHIEN	06FEB2009		
APVD W. KODAMA	06FEB2009	NAME	
PRODUCT SPEC 108-57519		TRIPLE STACKED USB, A TYPE, RECEPTACLE, R/A, DIP CONN.	
APPLICATION SPEC —			
WEIGHT 9.2 GRAMS	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734309
CUSTOMER DRAWING		SCALE —	SHEET 1 OF 3 REV. D2



WITHOUT SPRING



7	OBSELETE	2.84	2.84	BLACK (426C)	15μ"	5-1734309-7
7	OBSELETE			-BEIGE (726C)	15μ"	3-1734309-8
7	OBSELETE			BLACK (426C)	15μ"	3-1734309-7
7	OBSELETE			-BEIGE (726C)	30μ"	3-1734309-6
				BLACK (426C)	30μ"	3-1734309-5
			2.84	-BEIGE (726C)	5μ"	3-1734309-4
				BLACK (426C)	5μ"	3-1734309-3
				-BEIGE (726C)	G/F	3-1734309-2
				BLACK (426C)	G/F	3-1734309-1
		2.2		-BEIGE (726C)	15μ"	1-1734309-8
				BLACK (426C)	15μ"	1-1734309-7
				-BEIGE (726C)	30μ"	1-1734309-6
				BLACK (426C)	30μ"	1-1734309-5
			2.2	-BEIGE (726C)	5μ"	1-1734309-4
				BLACK (426C)	5μ"	1-1734309-3
				-BEIGE (726C)	G/F	1-1734309-2
				BLACK (426C)	G/F	1-1734309-1
		DIM B	DIM A	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	CHK	TE Connectivity	
	0 PLC ± -	APVD		NAME	
	1 PLC ± 0.30	PRODUCT SPEC		TRIPLE STACKED USB, A TYPE, RECEPTACLE, R/A, DIP CONN.	
	2 PLC ± 0.25	APPLICATION SPEC		SIZE	CAGE CODE
	3 PLC ± 0.20	WEIGHT 9.0 GRAMS		DRAWING NO	RESTRICTED
	4 PLC ± -	CUSTOMER DRAWING		A3 00779	C=1734309
MATERIAL	FINISH	SCALE	SHEET 2 OF 3	REV D2	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

LOC

DW

2

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD




SEE SHEET 1.

4


3

1

100PCS/TRAY




10 LAYERS



CARTON

TAPE



13.0	12.0	100	10	1000
G/W (KG)	N/W (KG)	PCS/ TRAY	TRAY/ CARTON	PCS/ CARTON

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH

NAME



TE Connectivity

TRIPLE STACKED USB, A TYPE,
RECEPTACLE, R/A, DIP CONN.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734309

SCALE

SHEET

3 OF 3

REV D2