




# 2012J-254 open type ( 7600-B )



## NOTES

### 1.MATERIAL

1.1 Insulator:PBT+15% G.F. UL-94V-0

### 2.SPECIFICATION

2.1 Current Rating: 3Amp

2.2 Dielectric Withstading : AC 500V/min.R.M.S.

2.3 Insulator Resistance: 1000M ohms Min

2.4 Contact Resistance: 20 M ohms Min

2.5 Operation Temperature: -55 °C to +85 °C

| REV. | NOTES    | DATE       |
|------|----------|------------|
| A    | RELEASED | 2003/10/05 |
| B    | 增加料號     | 2004/5/05  |
| C    | 增加0.30尺寸 | 2004/10/26 |
| D    | 增加料號     | 2004/11/24 |

## ORDER INFORMATION

| Part No.     | Color            | Contact         | Plating            |
|--------------|------------------|-----------------|--------------------|
| AMJ-B060B-0  | Black            | Brass           | Gold/Nickel Plated |
| AMJ-B060B-09 | Black            | Brass           | Gold/Nickel Plated |
| AMJ+B060B-09 | Black(NONTOXIC)  | Brass           | Gold/Nickel Plated |
| AMJ-B060B-03 | Black            | Brass           | 3u" Gold Plated    |
| AMJ-B060B-04 | Black            | Brass           | Tin Plated         |
| AMJ-B060B-06 | Black            | Brass           | 6u" Gold Plated    |
| AMJ-B060B-0B | Black            | Brass           | 30u" Gold Plated   |
| AMJ-B060B-R9 | Red              | Brass           | Gold/Nickel Plated |
| AMJ-B060B-R4 | Red              | Brass           | Tin Plated         |
| AMJ-B060B-R6 | Red              | Brass           | 6u" Gold Plated    |
| AMJ-B060B-Y9 | Yellow           | Brass           | Gold/Nickel Plated |
| AMJ+B060B-Y9 | Yellow(NONTOXIC) | Brass           | Gold/Nickel Plated |
| AMJ-B060B-59 | Green            | Brass           | Gold/Nickel Plated |
| AMJ-B060B-Q9 | Blue             | Brass           | Gold/Nickel Plated |
| AMJ+B060B-Q9 | Blue(NONTOXIC)   | Brass           | Gold/Nickel Plated |
| AMJ-B060B-99 | White            | Brass           | Gold/Nickel Plated |
| AMJ-P060B-09 | Black            | Phosphor Bronze | Gold/Nickel Plated |
| AMJ+P060B-09 | Black(NONTOXIC)  | Phosphor Bronze | Gold/Nickel Plated |
| AMJ-P060B-06 | Black            | Phosphor Bronze | 6u" Gold Plated    |
| AMJ-P060B-0E | Black            | Phosphor Bronze | 10u" Gold Plated   |
| AMJ-P060B-R9 | Red(NONTOXIC)    | Phosphor Bronze | Gold/Nickel Plated |
| AMJ+P060B-R9 | Red              | Phosphor Bronze | Gold/Nickel Plated |
| AMJ-P060B-Y9 | Yellow           | Phosphor Bronze | Gold/Nickel Plated |
| AMJ+P060B-Y9 | Yellow(NONTOXIC) | Phosphor Bronze | Gold/Nickel Plated |
| AMJ-P060B-59 | Green            | Phosphor Bronze | Gold/Nickel Plated |
| AMJ-P060B-Q9 | Blue             | Phosphor Bronze | Gold/Nickel Plated |
| AMJ-P060B-99 | White            | Phosphor Bronze | Gold/Nickel Plated |
| AMJ-P060B-Q4 | Blue             | Phosphor Bronze | Tin Plated         |
| AMJ-B060B-05 | Black            | Brass           | 5u" Gold Plated    |
| AMJ+B060B-09 | Black            | Bronze          | Gold/Nickel Plated |

(ROHS)

| 單位(UNITS)  | mm       | Top Willing Co., Ltd. |    |                |   |
|------------|----------|-----------------------|----|----------------|---|
| 數量(QT' Y)  | N/A      |                       |    |                |   |
| 材料(MT' L)  | SEE NOTE | 圖名(NAME)              |    |                |   |
| 處理(FINISH) | SEE NOTE |                       |    |                |   |
| 繪圖(DRAW)   |          | MJ 6B黑色 青銅半面金         |    |                |   |
| 設計(DE' N)  |          | 料號(PART NUMBER)       |    | AMJ-B060B-0    |   |
| 審校(CH' K)  |          | 圖號(DRAW NUMBER)       |    | RAMJB060B0     |   |
| 核准(APP' D) |          | 圖檔(FILE NAME .DWG)    |    | E:GCT/A/MJ/060 |   |
| 比例(SCALE)  | 1/1      | 圖紙(SIZE)              | A4 | 頁次(SHEET)      | 1 |
| 版次(REV.)   |          | 版次(REV.)              |    | 版次(REV.)       |   |

| DIMENSIONS TOLERANCE |
|----------------------|
| METRIC               |
| .0= ±.20             |
| .00= ±.10            |
| .000= ±.XXX          |
| .0000=±              |
| ANG.= ±2°            |