

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39544-5011

Status:


Active

Overview:

Eurostyle™ Terminal Blocks

Description:

5.08mm Pitch Eurostyle™ Vertical Fixed Mount PCB Terminal Block, with Standard Imprinting, 11 Circuits



Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39544

N/A

with Standard Imprinting

One Piece

Eurostyle™ Terminal Blocks

ESE, Eurostyle™Fixed Mount

Euro Block

822350547604

Physical

Circuits (Loaded)

Entry Angle

Lock to Mating Part

Number of Rows

Orientation

PC Tail Length

PCB Thickness - Recommended

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

11

Horizontal

None

1

Vertical

3.00mm

2.00mm

No

5.08mm

5.08mm

N/A

No

-40°C to +105°C

12, 14, 16, 18, 20, 22

0.33 - 3.31

Electrical

Current - Maximum per Contact

Voltage - Maximum

15A

300V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-free Process Capability

Max. Cycles at Max. Process Temperature

Process Temperature max. C

5

Wave Capable (TH only)

135

260

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-39544-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39544Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39544-5011](#)