







PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR MATERIAL: PBT
FLAMMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: SELECTIVE GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES

LED COLOR
LED 1: BIPOLAR GREEN/YELLOW
LED 2: BIPOLAR GREEN/YELLOW

ENVIRONMENTAL
OPERATING TEMPERATURE: -40°C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.5 A
WORKING VOLTAGE: 120 VAC
INSULATION RESISTANCE: >500 MΩ
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MIN
CONTACT RESISTANCE: 20 mΩ MAX

STANDARD
CERTIFIED: E324776


SOLDERING
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
TRAY

RoHS Compliant

G	17-JUL-14	CHARACTERISTICS	AS
F	03-JAN-14	UL & TEMP UPDATE	QL
E	20-AUG-13	DIM UPDATE	QL
D	27-FEB-09	LED COLORS	JP
C	06-MAY-08	LED SYMBOL	CH
B	22-APR-08	LED COLORS	CH
A	01-APR-08	PDF	CH
REV	DATE	FILE	BY

PROJECTION:



APPROVAL: RJ

GENERAL TOLERANCE

.X = +/_ 0.2

.XX = +/_ 0.15



UNIT: MM

SCALE:

SHEET: 1/1

DRAW:

DESCRIPTION: HORIZONTAL SHIELDED WITH BIPOLAR LED AND EMI PANEL
FINGER 8P8C MODULAR JACK TAB UP

WERI PART NO: 615 008 141 321

SIZE

A4